



A WORLD LEADER IN FUME  
EXTRACTION TECHNOLOGY

# DentalPRO Xtract 200

Last Updated on 02.02.2022



Dust and fume extraction cabinet for dental laboratory applications.

BOFA's DentalPRO Xtract 200 dust and fume extraction cabinet is designed for the removal of dust and fumes generated during dental hand finishing or monomer mixing applications.

This unit is ideally suited to manual benchtop applications and provides technicians with the flexibility to work without restriction in the knowledge that dust particles and fumes are being removed to maintain a safe working environment.

This system combines maximum technician protection in a small footprint, with scalable and flexible options.

## Technology



ProTECT service  
plan



SureCHECK  
quality standard

## Key features of the DentalPRO Xtract 200

**Easily replaced screen protector ensures clear visibility at all times**  
Standard

**Side entry grommets for mains powered hand finishing units**  
Standard

**Strong rigid construction**  
Standard

**DentalPRO 250 filtration system**  
Optional

**DentalPRO Mono filtration system**  
Optional

**Internal LED strip light**  
Standard

**Removable collection tray**  
Standard

**Powder coated white**  
Standard


**DentalPRO 400 filtration system**  
Optional

Contact BOFA at <https://bofainternational.com/en/contact/>  
<https://bofainternational.com/en/portal/datasheets/dentalpro-xtract-200/>





Approvals: REACH and RoHS. See individual product technical data for specific accreditations

## Technical specification



## Airflow through filters



## Technical data

	EU	US
Dimensions	355 x 540 x 400mm	13.98 x 21.26 x 15.75"
Opening dimensions (HxW)	315 x 540mm	12.4 x 21"
Recommended face velocity	0.5m/s	150 f/min
Approvals	UKCA and CE	UKCA and CE

## Cabinet part numbers

Model	Part number
DentalPRO Xtract 200	D0946A0000

## Hose kit part numbers (needed if ordering extraction system)

Description	Part number
Hose kit to connect extraction system to DentalPRO Xtract cabinet	A1020068

## Extraction system part numbers

DentalPRO 400			
Model	Option	Voltage	Part number
DentalPRO 400 powder coated unit twin port 75mm lid		90V - 257V	DL0944A0000
DentalPRO 400 powder coated unit twin port 75mm lid	24V stop / start override siler change signal	90V - 257V	DL0944A0001
Unit options			
Foot switch (on / off operation)			A1070184
DentalPRO 250			
Model		Voltage	Part number
DentalPRO 250 powder coated unit single port 75mm lid		230V	DL0142A0000
DentalPRO 250 powder coated unit single port 75mm lid		115V	DL0141A0000
DentalPRO Mono			
Model		Voltage	Part number
DentalPRO Mono powder coated unit single port 75mm lid		230V	DL2043A0000
DentalPRO Mono powder coated unit single port 75mm lid		115V	DL2041A0000

**Other hose kits and filters are available.**

*Datasheet correct at time of publishing.*

*Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOCs, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.*

**Important Notice:** Many factors beyond the control of BOFA can affect the use and performance of BOFA products in a particular application, including the conditions under which the product is used. Since these factors are uniquely within the user's knowledge and control, it is essential the user evaluate the products to determine whether the product is fit for the particular purpose and suitable for the user's application. All products, product specifications, availability and data are subject to change without notice, and may vary by region or country.

*Think before you print! Please consider the environment before printing this document.*