

## **AD 1000 Pro OS Connect**

Fume Extraction System - Advantage Range

### **Datasheet**

**Technical Specification and Product Information** 

An extraction system for medium to heavy-duty laser applications.

The AD 1000 Pro OS Connect fume extraction system is an ideal choice for applications that generate high levels of particulate. Equipped with our new, innovative Pro OS software platform, this intuitive system takes productivity to the next level.


#### **FEATURES**


- Two-way data stream
- Color touch screen
- Real-time system status
- Multi-language software
- Customizable branding

Approvals: UK and CE | cUL | UL\*

- Filter life monitor
- Pressure sensors
- Alarm configurations
- USB lock screen

# TECHNICAL SPECIFICATION





- 1. Touchscreen display
- 2. On/off switch
- 3. Power cable
- 4. Signal/interface cable
- 5. Door hinges
- 6. Hose inlet connection 2.95" (75 mm)
- 7. Exhaust outlet

- 8. RJ45 ethernet port\*\*
- 9. Door latches
- 10. Castors
- 11. USB port
- 12. Blower cooling outlet
- 13. Overcurrent trips (115 V only)

#### **TECHNICAL DATA**

Voltage	Unrestricted airflow*** (+/- 10%)		Settable airflow range****		Pressure (+/- 6%)	Dimensions (H x W x D)		Weight (+/- 5%)		Noise level****	Lroallonov.	Full load current
V	cfm	m³/hr	cfm	m³/hr	mbar	in	mm	lbs	kg	dB(A)	Hz	amps
115	515 875	875	177-430	300-730	65	47.4 x 24.6 x 31.7	1205 x 625 x 805	309	140	< 70	50/60	19.5
230	515	0 0/0	177-459	300-780	60						50	12.8

#### **AIRFLOW**

Pre-filter


HEPA filter

Chemical filter

Clean filtered air

Contaminated air





#### **PART NUMBERS - SYSTEM**

Description	Part number
Stainless steel, 230 V 24 V S/S, SOK, VOC, UK Plug	1U8700106705
Stainless steel, 230 V 24 V S/S, SOK, VOC, EU Plug	1U8705106705
Stainless steel, 115 V 24 V S/S, SOK, VOC, USA Plug	1U8710105705
Powder-coated, 230 V 24 V S/S, SOK, VOC, UK Plug	1U8700811705
Powder-coated, 230 V 24 V S/S, SOK, VOC, EU Plug	1U8705811705
Powder-coated, 115 V 24 V S/S, SOK, VOC, USA Plug	1U8710810705

#### FILTER SPECIFICATIONS

Model	Surface m (app	Filter	
	ft²	m²	efficiency
DeepPleat DUO pre-filter	322.8	30	ePM1 70%
Combined filter (HEPA)	80.7	7.5	99.995% @ 0.3 microns

Model	Activated carbon volume		
Model	ltr		
Combined filter (gas)	53.7		

#### **PART NUMBERS - FILTERS**

DeepPleat DUO pre-filter	Combined filter
1UA1030222	1UA1030297

Cabinet construction

Brushed stainless steel
Powder-coated mild
steel (RAL7016)

Compatible accessories:

Spark Arrestor 2 ILF 600

Germany

Datasheet correct at time of publishing. Where applicable, the carbon used in Donaldson BOFA systems is capable of removing a wide range of VOCs, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

#### Important Notice

Many factors beyond the control of Donaldson can affect the use and performance of Donaldson products in a particular application, including the conditions under which the product is used. Since these factors are uniquely within the user's knowledge and control, it is essential the user evaluate the products to determine whether the product is fit for the particular purpose and suitable for the user's application. All products, product specifications, availability and data are subject to change without notice, and may vary by region or country.



Approvals: REACH and RoHS. See invididual product technical data for specific accreditations.



Donaldson BOFA

UK & ROW Tel. +44 (0) 1202 699 444 Email. bofasales@donaldson.com Web. donaldsonbofa.com

Email. bofavertrieb@donaldson.com

USA Tel. +1 (618) 205 5007 Email. bofasalesus@donaldson.com

ENG (January 2025) Donaldson BOFA AD 1000 Pro OS Connect Datasheet. ©2011-2025 Donaldson Company, Inc. Donaldson, Torit, Dalamatic, Delta P, Delta P Plus, Downflo Dura-Life, Easy Duct, PowerCore, Synteq XP, Ultra-Web, Unimaster and the color blue are marks of Donaldson Company, Inc. All other marks belong to their respective

<sup>\*</sup>UL: Tested to UL standards, but testing may be provided by alternate nationally recognized test laboratories. Certain product configurations may affect the UL certification. Please speak to your sales representative.

<sup>\*\*</sup>Connectivity: The Pro OS models feature connectivity via an RJ45 port which is located on the rear of the extraction system. This port can be used as 2-way communication, enabling the control of the extraction system as well as live data streaming from the system. For information on how to configure your device to communicate with the Pro OS, please use document: SG-PRO OS CONNECT PROTOCOL CONFIGURATION GUIDE-BOFA-US

<sup>\*\*\*</sup> Unrestricted airflow: The airflow values provided with clean filters, no hose kit, at 230 V, measured by using a wind vane. The numbers may vary depending on voltage and test procedure used.

<sup>\*\*\*\*</sup> Settable range: Donaldson BOFA recommends utilizing the lowest flow rate that achieves the correct capture velocity for your application in order to maximize filter life.

<sup>\*\*\*\*\*</sup> Noise level: At typical operating speed.